


Containment Drum-Dispensing into FIBC's; OEB 5

For limited room height of 3600mm!



1. Drum in docked position to the isolator. Docking with SmartDock
2. Push-Filter for exhaust air
3. Push-Filter for inlet air
4. Hydraulic drive movement to move the tilted drum to, and away from the SmartDock
5. Isolator with hinged glass door
6. Bag out port to remove the shower cap of the last drum
7. Powder outlet into BigBag-filling. Isolator in a position for optimized ergonomic operating with a very limited room height
8. Decoupling compensator between Isolator and BigBag-filling system which is on a scale
9. SmartDock for containment BigBag filling
10. Height adjustable platform for different operators
11. BigBag-frame on the scale
12. Platform with stair and space around the system for optimized ergonomic operating
13. Stationary lifting device with automatic drives for
 - 13.1. Lifting / Lowering
 - 13.2. Step less tilting
 - 13.3. Horizontal movement of the drum
14. Floor scale

- Containment Docking
- Solids calibration
- Lift-and Tilting devices
- Container-and Drum Blending

CH-4431 Bennwil
 Tel. +41-(0)61-956 91 91
 Fax +41-(0)61-956 91 90
 info@rubitec.ch
 www.rubitec.ch

rubitec ag